



# THE ACCELERATOR SITE SURVEY BATTERY PACK VERSION 0



The AccelTex Solutions new battery pack—*The Accelerator*— was specifically designed for use at site surveys. Its small, compact design and battery capacity allows for many hours of continuous use. It is the ultimate site survey tool and is a must-have for all Wi-Fi engineers.

**NOTE: This version of the Accelerator is not 802.3 Compliant**

Part Number: ATS-SSBP-0



## FEATURES

- Multiple PoE outputs
- Lightweight and portable
- Charge while in use
- LCD Display toggles between battery percentage and voltage



## BENEFITS

- Provides isolated and uninterrupted power
- Compact and portable



## NORMAL OPERATION

- The 5V USB output port is power only
- Charge the battery pack to 100% before first use
- Do not plug 2.1mm wall charger connector into the 12V output port
- Turn on 5V USB by moving the toggle switch to either “48V” or “24V”
- To use PoE output, simply slide the toggle to the port you want to use



## IMPORTANT NOTES

- The USB port is only active when the toggle switch is in the “48V” or “24V” position
- The 12V output is always on
- Turn toggle switch to the “OFF” position when not in use. If you leave the toggle switch in the “48V” or “24V” position, it will gradually drain the battery
- Use only the wall charger supplied with the battery pack. Do not use an after-market or third party wall charger.
- Based on FAA and U.S. DOT regulations, when traveling by plane, *The Accelerator* can be transported in a carry-on bag while in its carrying case. TSA Security, individual airline and international rules may, at times, be more restrictive



LCD Display



Battery in Portable Carrying Case



## APPLICATIONS

- Performing wireless site surveys
- Portable IP camera set-ups
- Temporary wireless bridge connections
- Charge mobile phones and tablets



## INCLUDED IN BOX

- *The Accelerator* battery pack
- Portable carrying case
- Wall charger
- 2.1mm male-to-male connector (12V output)



## BATTERY NOTES

- *The Accelerator* battery pack falls under United Nations regulation UN3481
- Since *The Accelerator* is under 100Wh in rating, it can ship via FedEx air when labeled properly

The facts and figures herein are carefully compiled to the best of our knowledge and are intended for general informational purposes only. Responsibility for the use and application of AccelTex Solutions materials rests with the end user. All AccelTex Solutions products are sold pursuant to the AccelTex Solutions Terms and Conditions of Sale. © 2020 AccelTex Solutions. All Rights Reserved. AccelTex, AccelTex Solutions, the AccelTex Solutions Logo and other marks are trademarks or registered trademarks of AccelTex Solutions. Other products or service names may be the property of third parties.

1.888.406.8906

SALES@ACCELTEX.COM

# THE ACCELERATOR SITE SURVEY BATTERY PACK VERSION 0

Part Number: ATS-SSBP-0



## MECHANICAL SPECIFICATIONS

Battery Dimensions: 5.3" H x 3.9" W x 1.7" D (135 mm H x 100 mm W x 43 mm D)  
Battery Color: Black  
Battery Weight: 1.32 lbs. (0.6 kg)



## ELECTRICAL SPECIFICATIONS

Operating Voltage: 110 - 220V  
Battery Input (2.1mm): 12.6V DC, 2A  
Battery Output (2.1mm): 12V, 2A  
LAN Input: 10/100  
PoE Output:


- Port 1: 48V, 0.5A (non 802.3 compliant)
- Port 2: 24V DC, 1A Passive PoE

USB 2.0 Output: 5V DC, 2A  
Battery Type and Capacity: Li-Ion 7500 mAh 12.6V/94.5Wh  
Battery Recharge Time: 4 hours



## ENVIRONMENTAL SPECIFICATIONS

Operational Environment: Indoor/Outdoor. Do not directly expose to inclement weather conditions.  
Operating Temperature: 14 to 140°F (-10 to 60°C)



# THE ACCELERATOR SITE SURVEY BATTERY PACK VERSION 0

Part Number: ATS-SSBP-0



## WALL CHARGER INDICATOR LIGHTS



**BLUE** = Battery is fully charged



**RED** = Battery is charging

NOTE: If the light is flickering between Blue and Red, this may occur when a battery pack is charged to 100% while a device is connected.

## TRAVEL NOTES

- Since The Accelerator is under 100Wh in rating, it can ship via FedEx Air when labeled properly
- The Accelerator is compliant with United Nations regulation UN3481
- Based on FAA and U.S. DOT regulations, when traveling by plane, *The Accelerator* can be transported in a carry-on bag while it is in its carrying case. TSA Security, individual airline and international rules may, at times, be more restrictive
- If there is a concern about a specific country or airline, you will need to reach out to the respective country or airline to ensure compliance